

FORTUNA® OPTIMAT® 3 Dispensing Station - ready for your daily dosing tasks

The new design and the large touchscreen display show at first glance that the OPTIMAT dispensing station has been completely revised. Above all, we focused on the operating comfort. Furthermore, the user can accurately and reliably carry out serial dispensing in volume ranges from 0.05 - 300 ml. Even aggressive liquids, such as e.g. strong acids, can be easily handled with the dosing pumps that are made out of high quality materials such as borosilicate glass and PTFE.

The robust FORTUNA® OPTIMAT® 3 is perfectly suitable for continuous operation.



Poulten & Graf GmbH
Heide Fahrenkrog-Keller
Karl-Carstens-Str. 10

D-97877 Wertheim

Tel. 09342/9229-40
Fax.09342/9229-80
H.Fahrenkrog-Keller@poulten-graf.com

www.poulten-graf.de